


Liverpaste batter – baking tin filling

FILLFLEX
– the flexible filling machines



Liverpaste batter is filled in aluminium tins. The tins are placed on baking trays on a trolley, which is rolled into the oven for baking.

Solution

We recommended a Fillflex Compact that sucks liverpaste batter from the storage vat. With a hand-held ejector the tins are filled, one after another. Both start and stop of the fillings are controlled by the machine. The time between stop and start is set so that the operator can move the ejector to the next tin.

Advantages

- high reliability of service
- low investment costs
- easy to change filled volume and time between fillings
- space-saving and easy to put in place



Telfafill Compact sucks liverpaste batter from the storage vat.



Telfafill Compact has a space-saving design and is easy to put in place.



The machine starts automatically after the pre-set time.

The machine has been used on daily basis for several years and has considerably increased the filling efficiency.

Selected filler and equipment

Filling machine: F5500C28320

Outlet hose: TFA 10135-20

Suction hose, hose nipple, nut and gaskets.